型号: YGH 6246说明书

图纸编号: YGH-QM-03-A292

尺寸: 60*73mm

版本号: A-0

材质: 80g书写纸 正反印刷 风琴折

月期: 2025.09.08



Temperature and Humidity Monitor




Model: YCN-H202R

Diagramm




) (°C/°F) (

- 1. Humidity Display 2. Temperature Display
- 3. Comfort Level: DRY/COMFORT/WET 4. Face Icon (Air comfort
- indicator) 5. Battery Icon
- 6. Vent hole (Note: Please do not block the vent hole when installing and using The product.)
- 7. Hanging Hole
- 8. Magnet 9. °C/°F
- 10. Battery buckle (The bracket is included inside)



Placement Ways

- 1. Attach it to any metal surface directly.
- 2. Hang it up with the coming lanyard.
- 3. Place it on desktop with the bracket.



Features

- 1. Display: LCD display, Humidity, Temperature
- 2. Humidity Display Range: 10%~99%
- 3. Temperature Range: -9.9°C~60.0°C (14.2°F~140°F)
- 4. Comfort Level: DRY/COMFORT/WET
- 5. Totally wireless tabletop and magnet mountable design: And you can use a lanvard to hang temperature humidity monitor in the desired place
- 6. Battery: Holds on a AAA battery to power

Comfort Level

DRY	Humidity is below 29% (<10%, 10-20%, 21-29%)	
COMFORT	Humidity is between 30%-69% (30-39%, 40-60%, 61-69%)	
WET	Humidity is above 70% (70-79%, 80-89%, 90-99%)	

Face Icon Meaning

	Temperature <19°C (Below 66.2°F)	19°C≤Temperature ≤27°C (Between 66.2°F and 80.6°F)	Temperature >27°C (Above 80.6°F)
Humidity <30%	©	<u> </u>	3
30%≤ Humidity ≤70%	·	⊖	<u>•</u>
Humidity >70%	(3)	©	(3)

Temperature

- 1. Temperature Range:-9.9°C~60°C(14.2°F~140°F)
- 2. Temperature Accuracy: $\pm 1^{\circ}$ C(0~40°C), ±2°C(40~60°C)
- 3. Refresh Rate: 10 seconds
- 4. Temperature Resolution: 0.1°C(0.1°F)
- 5. If the temperature is lower than -9.9°C, display: -9.9°C;if higher than 60°C, display: 60°C

Humidity

- 1. Humidity Range: 10%~99% RH
- 2. Humidity Accuracy: ±3%~5%RH
- 3. Refresh Rate: 10 seconds
- 4. Humidity Resolution:1%
- 5. If the humidity is below 10%, display: 10%; If above 99%, display: 99%

Battery Tips

When the power is low, the battery icon [🗓] will appear and remind you to replace the new battery.

Battery Replacement

- 1. Open the battery cover from the Battery buckle.
- 2. Insert or replace one AAA battery into the battery compartment with correct polarity (+) and (-) as shown.
- 3. Insert the battery cover.

°C/°F Switch

Press the [°C/°F] button to switch temperature unit to°C/°F.

Warning

- 1. Please operate this product under the operating instructions. Do not expose the unit to extreme temperatures, direct sunlight, dust, humidity and soon.
- 2. Do not disassemble the device privately.
- 3. Please use a AAA battery to supply for this humidity meter. And please take the battery out when not in use.
- 4. Please prevent the product from falling.
- 5. This product is non-waterproof, please stay away from any liquid.
- 6. When the screen display is unclear, please replace the battery.



Mediaonderdelen.nl Duinkerkenstraat 9 UNIT C 9723 BN Groningen info@vuconn nl













